

### **Product Overview**





Carry handle for easy transport

Removable hand wand for detail cleaning

Onboard storage for accessories

# **Product Specification Sheet**






Max sealed suction	12kPa
Max air volume	1.9m³/min
Capacity	5L
Continuous runtime (min) BL1860B x 2	30 minutes
Skin weight	7.8kg
Weight with batteries	9.0kg
Voltage	18Vx2 (36V)

- Powerful Suction high performance suction for efficient use in the toughest applications
- Detail Cleaning Removeable hand wand and flexible hose for cleaning away from the vacuum
- 3 Stage Suction Control Allows the user to achieve optimum runtime and suction power for their task
- HEPA Filter provides a high filtration rate of 99.97% at 0.3 micron
- Quiet Mode Operates at just 60dB on lowest speed setting to limit disturbance to nearby people
- Easy Maintenance Tool free brush change for easy maintenance on the go
- On-board Storage crevice nozzle and round brush are secured in the back of the vacuum for easy access



#### **Power**



18Vx2 Brushless motor provides AC like power for the toughest applications

#### **Convenience**



Tool free brush change for maintenance on the go

### **Ergonomics**



90° range of operation for use at any angle and under furniture

### **Efficiency**



3 speed brush and vacuum selection for optimum control of power and runtime



### Convenience

Brush maintenance has been made easy by simply unclipping the brush cover assembly and sliding the brush out from the housing.

The brush itself has wide grooves between each strip of bristles to allow hair & fabric to be cut away and removed with minimal effort.





### Power



High efficiency brushless motors drive the airflow fan and power brush independently to ensure maximum suction & torque under any application.



### **Ergonomics**

90° operation allows for vacuuming under low furniture and locking in a stable upright position for storage and while the hand wand is being used for detail cleaning.

It also allows for comfortable operation by users of a wide range of heights.





# Accessories



Standard Accessories		
	191D65-8	330mm Crevice Tool
	191D67-4	Round Brush
	-	Disposable Filter Bag 1pce
	191E39-5	HEPA Filter
	191D69-0	Main Brush Assembly

<b>Optional Accessories</b>		
	191T96-3	Filter Bag Set Disposable 10pk

### **Frequently Asked Questions**



#### **How do I clean the HEPA Filter?**

The HEPA Filter should be regularly cleaned to maintain optimum performance. Remove the filter from the unit and tap the filter to remove any loose dust. The filter can be washed with water, however, make sure it is completely dry before using again. Never use high pressure air or hard brushes as these can damage the filter.